



Configuration #GP2AP-SHF510-50G
Elevating Table with Floor Mount Rotate Tube Stand
with 50 kW Generator and 50G Portable Digital Panel

SHF 510AP-GI 50 kW, 500 mA, 500 mAs High Frequency Generator

- 500 mA., 125 kVp (500 mA. @100 kVp)
- Eighteen mA stations, 10, 12.5, 16, 20, 25, 32, 40, 50, 64, 80, 100, 125, 160, 200, 250, 320, 400, 500
- 0.001 to 10 second timing
- kVp selection, 40 to 125 kVp in 1 kV increments
- Digital displays
- Automatic line compensation
- APR, Anatomical Programming
- AEC Electronics and (2) ion chambers
- Generator integration with acquisition monitor
- Exposure hand switch
- UL/CE/FDA Listed
- **For Operation on 1 Phase 220/240VAC, see option for 3 phase**

S-HL Elevating, Four Way Float Top Table -750 Lb. Patient Load

- 86.5" x 31.5" float table top
- 43.3" longitudinal and 9.5" lateral table top travel
- Collision protection

RECEPTOR/ ACQUISITION/ GRIDS Canon CXDI-50G Portable DR Panel, includes;

- 14" x 17" (35cm x 43cm) imaging area
- GOS scintillator, LANMIT 4 sensor, a-Si TFT panel
- 2208 x 2688 pixel array (5.9 million pixels)
- 160 micron x 160 micron high resolution pixel pitch
- 12 bit/4096 gray scale contrast
- Preview image in about 5 seconds
- Power Supply and Ethernet interface
- Dual mode landscape/portrait DR cabinets (Qty. 2)
- 10:1 ratio grid for DR cabinet (Qty. 2)
- 10:1 ratio snap-on portable grid
- 19" Touch screen monitor with generator integration
- Computer, 80 GB
- DICOM 3.0 compliant
- DICOM Modality Worklist
- Canon LANMIX MLT processing software
- Keyboard
- Mouse

S-FMT Floor Mount Tube Stand

- 11.8" Transverse travel, 180° rotation, vertical travel 15.7" to 74.75"
- Platform tube mount
- Electromagnetic brakes for longitudinal, transverse, vertical & rotation
- 86.6" floor track provides 58.3" longitudinal tube travel

MIL-WH Wall Stand

- Floor to Wall Mount with magnetic locks (84" column)

E7884FX X-Ray Tube - 300,000 Heat Unit - 90° cable arms, 150 kVp, 0.6-1.2mm focal spot, 3" anode, 14" target, LS

70-63000-6 Manual Collimator, Includes

- Molded plastic housing
- Bucky centering light
- Tape measurer

10526-25 Cables, Pair - 25' long



Configuration #GP2AP-SHF510-50G

Elevating Table with Floor Mount Rotate Tube Stand with 50 kW Generator and 50G Portable Digital Panel

Generator Options:

PED	Pedestal for control console, replaces table mount
CP	Wall mount for control console, replaces table mount
SHF 520AP	50 kW, 125 kVp 3 phase, 220VAC
SHF 525AP	50 kW, 150 kVp 3 phase, 220VAC
SHF 545AP	50 kW, 150 kVp 3 phase, 480VAC
SHF 645AP	64 kW, 150 kVp 3 phase, 480VAC, replaces 50 kW
SHF 845AP	80 kW, 150 kVp 3 phase, 480VAC, replaces 50 kW
HSS-1T	High speed starter, 1 tube

Receptor Option:

CXDI-55G	Portable DR Panel, replaces 50G
RADAX	Rotating DR cabinet, replaces landscape/portrait cabinet

Acquisition Options: See page 47 for additional upgrade options

Wall Stand Options:

TE-11	Tilt mechanism
-------	----------------

Tube Options:

E7254FX	400,000 H.U., 150 kVp, 0.6-1.2mm tube, replaces E7884FX
E7869FX	600,000 H.U., 150 kVp, 0.6-1.2mm tube, replaces E7884FX

Collimator Options:

SM-302A-2	Automatic collimator replaces, manual collimator
-----------	--

Assistance:

AST-DR	(Does not include travel and expenses) Onsite assistance for DR panel
AST-APDR	Onsite applications training

